

Digital Hand-held "Pocket"

ATAGO®

# Honey Refractometer

PAL-22S Cat.No.4422



## The easiest, most objective way to check **honey** moisture



### Purpose of Use



- To check the quality of outgoing products
- To check the grades of incoming products

### How to Measure



1 Place the sample onto the prism surface.



2 Press the START key.



3 The measurement value will be displayed in 3 seconds.

### Accessories

- PAL-case  
Clipped to your belt



- PAL-strap



**Convenient!**



### Reason to choose PAL-22S



Digital display  
-no more boundary line



Calibration with water only  
-no more calibration liquids



Rinse under running water



Measurement time, only 3 seconds!



Measure indoors & outdoors



Temperature display



### Specification

Measurement Range	Honey Moisture 12.0 to 30.0%, Temperature 10.0 to 40.0°C
Resolution	Honey Moisture 0.1%, Temperature 0.1°C
Measurement Accuracy	Honey Moisture ±0.2%, Temperature ±1°C
Measurement Temperature	10 to 40°C (ATC*)
Ambient Temperature	10 to 40°C (ATC*)
Sample Volume	0.3ml or more
Measurement Time	3 seconds
Power Supply	2 alkaline batteries
Battery Life	Approx. 11,000 measurements (Using a new alkaline battery)
International Protection Class	IP65 Water Resistant
Dimensions and Weight	55 (W)×31 (D)×109 (H)mm, 100g (Main unit only)

\*ATC : Automatic Temperature Compensation

All ATAGO refractometers are designed and manufactured in Japan.

**HACCP GMP GLP**

ATAGO products comply with HACCP, GMP, and GLP system standards.

## ATAGO CO.,LTD.

Headquarters: The Front Tower Shiba Koen, 23rd Floor  
2-6-3 Shiba-koen, Minato-ku, Tokyo 105-0011, Japan  
TEL : 81-3-3431-1943 FAX : 81-3-3431-1945  
overseas@atago.net http://www.atago.net/

### ATAGO U.S.A., Inc.

TEL : 1-425-637-2107 customerservice@atago-usa.com

### ATAGO INDIA Instruments Pvt. Ltd.

TEL : 91-22-2833-8038 / 8076 customerservice@atago-india.com

### ATAGO (THAILAND) Co., Ltd.

TEL : 662-982-8718-9 customerservice@atago-thailand.com

### ATAGO BRASIL Ltda.

TEL : 55 16 3916-6000 customerservice@atago-brasil.com

### ATAGO ITALIA s.r.l.

TEL : 39 2 36557267 customerservice@atago-italia.com

### ATAGO CHINA Guangzhou Co., Ltd.

TEL : 86 20-38106065 info@atago-china.com



\* Specifications and appearance are subject to change without notice.

