

# Model BD-S 115 | Standard-Incubators with natural convection

The new products in the Solid.Line impress with their tried-and-tested BINDER quality and reliability. They are suited to incubation. The attributes of the Solid.Line are geared towards the application in question and therefore used in research and quality assurance.

## **BENEFITS**

- · Easy handling
- · Accurate temperature control
- · Simple and ergonomic door opening



Model 115

## MAIN FEATURES

- Temperature range: ambient temperature +5 °C to 70 °C
- APT.line<sup>™</sup> preheating chamber technology
- · Natural convection
- · Adjustable exhaust air flap
- · Controller with timer function
- Inner door made of tempered safety glass
- 1 chrome-plated rack, incl. shelf supports
- Class 3.1 integrated independent temperature safety device (DIN 12880) with visual alarm

## ORDERING INFORMATION

Interior volume [L]	Voltage	Option model	Version	ArtNo.
Model BD-S 115				
118	230 V 1~ ph 50/60 Hz	Standard	BDS115-230V	9090-0022
	120 V 1~ ph 60 Hz	Standard	BDS115UL-120V	9090-0023


#### **TECHNICAL DATA**

Description	BDS115-230V	BDS115UL-120V	
Article Number	9090-0022	9090-0023	
Performance Data Temperature			
Temperature range 5 °C above ambient temperature to [°C]	70	70	
Temperature variation at 37 °C [± K]	0.5	0.5	
Temperature fluctuation at 37 °C [± K]	0.2	0.2	
Recovery time after 30 seconds door open at 37 °C [min]	15	15	



Description	BDS115-230V	BDS115UL-120V
Article Number	9090-0022	9090-0023
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50/60	60
Nominal power [kW]	0.35	0.35
Unit fuse [A]	6.3	6.3
Phase (Nominal voltage)	1~	1~
Measures		
Interior volume [L]	118	118
Net weight of the unit (empty) [kg]	52.5	52.5
permitted load [kg]	75	75
Load per rack [kg]	20	20
Wall clearance back [mm]	160	160
Wall clearance sidewise [mm]	100	100
Doors		
Inner doors	1	1
Unit doors	1	1
Internal Dimensions		
Depth [mm]	390	390
Height [mm]	550	550
Width [mm]	550	550
Housing dimensions not incl. fittings and connections		
Width net [mm]	764	764
Height net [mm]	735	735
Depth net [mm]	616	616
Environment-specific data		
Energy consumption at 37 °C [Wh/h]	25	25
Fixtures		
Number of shelves (std./max.)	1/5	1/5

# DIMENSIONS incl. fittings and connections [mm]



# **OPTIONS AND ACCESSORIES**

Description	*	ArtNo.
T 220: For continuous temperature logging from -90 °C to 220 °C. The kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	19	8012-0715
LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	19	8012-0821
Incl. shelf supports		
chrome plated	-	8012-1808
concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-0016
set anti-slip feet	-	8012-1887
	T 220: For continuous temperature logging from -90 °C to 220 °C. The kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit  LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)  Incl. shelf supports chrome plated  concentrated, for gentle remove of residual contaminants; 1 kg	T 220: For continuous temperature logging from -90 °C to 220 °C. The kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit  LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)  Incl. shelf supports chrome plated  - concentrated, for gentle remove of residual contaminants; 1 kg

<sup>\*</sup> Notes > See last page



# **SERVICES**

Designation	Description	*	ArtNo.
Installation services			
Installation	and set up of unit at operating location, connect to existing connections	13, 18	DL10-0100
Instruction	unit function instructions for operation and programming of the controller	18	DL10-0500
Preventive maintenance			
Preventive maintenance	Executive of equipment inspection according to maintenance plan	14, 18	DL20-0200
Calibration services			
Calibration temperature incl. certificate	including certificate, one measuring point in center of chamber at specified temperature	14, 16, 17, 18	DL30-0101
Temperature measurement 27 measuring points	including certificate, 27 measuring points at specified temperature	14, 16, 17, 18	DL30-0127
Temperature measurement 9 measuring points	including certificate, 9 measuring points at specified temperature	14, 16, 17, 18	DL30-0109
Warranty service			
Extension of the warranty from 2 to 3 years	beginning with the date of delivery, wearing parts are not included	-	DL01-6041

<sup>\*</sup> Notes > See last page



#### **NOTES**

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- Heat resistant only to max. 200 °C. 03
- Only available on units rated for 230 V.
- Heating-up time may increase as a result of the lower heat conductivity.
- The additional heat input may affect the temperature behavior.
- Not in conjunction with the optional access port, door with window and interior lighting.
- Not available on 23-liter units.
- Not available on 23- or 53-liter units
- 10 11 12 Only available on units rated for 230 V or 400 V.
- Installation and connections take place at unit location; transport within the company only upon consultation.
- We recommend a BINDER service contract to cover unit inspections, calibrations and validations.
- OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory.
- 17
- Calibration is performed according to the BINDER factory standard.

  Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter.
- When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ folder.

When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.

BINDER GmbH Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd. Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

**BINDER Environmental Testing** Equipment (Shanghai) Co., Ltd. Shangha, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

Representative Office for CIS Moscow. Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.ru

BINDER Inc. Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us