

Compact Balances

EJ

Series



EJ-1500



EJ-120

The EJ Series compact balances are specifically designed for on-line and catalog sales. Their performance and functions are also ideally suited for the education market.

- Unique and eye-catching color design.
- Hygienic and rustproof stainless steel pan.
- Supports multiple weighing units.
- Slot in the rear for an anti-theft lock.
- Stackable body to save storage space.
- Calculates density automatically.*

* The optional density determination kit (EJ-13) is required.



Stackable body



A&D
A&D Australasia

"Excellence in Measurement"

www.andaustralasia.com.au

Compact Balances *EJ* Series

Specifications

	EJ-123	EJ-303	EJ-120	EJ-200	EJ-300	EJ-410	EJ-610	EJ-1500	EJ-2000	EJ-3000	EJ-4100	EJ-6100	
Weighing capacity	120g	300g	120g	210g	310g	410g	610g	1500g	2100g	3100g	4100g	6100g	
Min. weighing value	0.001g		0.01g					0.1g					
Weighing units	g, pcs, %, oz, lb, ozt, ct, mom, dwt, GN, N, SG (density), tola*, tael, (HG, HJ, T)*												
Counting mode	Max count**	120,000 pcs	310,000 pcs	12,000 pcs	21,000 pcs	31,000 pcs	41,000 pcs	61,000 pcs	15,000 pcs	21,000 pcs	31,000 pcs	41,000 pcs	61,000 pcs
	Min. unit weight**	0.001g		0.01g					0.1g				
	No. of samples	5, 10, 25, 50 or 100 pieces											
Percent mode	Min. % display	0.1%											
	Min .100% weight	0.1g		1g					10g				
Repeatability (standard Deviation)	0.003g	0.001g	0.1g										
Linearity	±0.0003g		±0.01g		±0.02g		±0.02g		±0.1g		±0.2g		
Sensitivity drift	±20ppm/°C to 30°C / 50°F to 86°F												
Display type	7-segment LCD with backlight (character height 16mm)												
Display refresh rate	10 times per second												
Operating temperature	-10°C to 40°C / 14°F to 104°F, 85%RH or less (no condensation)												
Power supply	AC adapter or 4 x AA batteries												
Battery operation	Approximately 70 hours (backlight off, alkaline batteries)												
Calibration mass**	100g	300g	100g	200g	300g	400g	600g	1500g	2000g	3000g	4000g	6000g	
Weighing pan size	Ø110mm						127mm x 140mm						
Net weight	Approximately 850g						Approximately 970g						

* For special version only. One of them can be selected or installed at the factory.
** Factory setting

Options

EJ-13



EJ-11




- EJ-02** Quick USB interface
- EJ-03** RS-232C interface
- EJ-07** Underhook for EJ-3000 / EJ-4100 / EJ-6100
- EJ-08** Underhook for EJ-1500 / EJ-2000
- EJ-11** Breeze break
- EJ-12** Carrying case
- EJ-13** Density determination kit for EJ-120 / EJ-200 / EJ-300 / EJ-410 / EJ-610



EJ-12

Dimensions(mm/inches)



EJ-120/200/300/410/610

EJ-1500/2000/3000/4100/6100

A&D
A&D Australasia
"Excellence in Measurement"

ACN 007 556 809
Head Office
32 Dew Street
THEBARTON South Australia 5031
Telephone (08) 8301 8100
Facsimile (08) 8352 7409

Victorian Office
39 Bakehouse Road
KENSINGTON Victoria 3031
Telephone (03) 9372 1522
Facsimile (03) 9372 1193

Email: sales@andaustralasia.com.au
Internet page: www.andaustralasia.com.au

New South Wales Office
Unit 4, 14 Abbott Road
SEVEN HILLS New South Wales 2147
Telephone (02) 9674 5466
Facsimile (02) 9674 2544

Your Dealer